



BAAK

Fußgerechte **Sicherheit**

From range Baak Bau

Article 22402 Andy2

Half shoe

S3 SRC ESD



certified for
orthopedic insoles
for details www.baak.de/en




Knee- & Backfriendly
Scientifically evaluated

**Foot conform
fitting & function**

Upper	High quality smooth genuine cow leather, black, in combination with attractive green textile, padded edge Lining: high quality textile counter- and leather vamp lining Tongue: closed padded Lacing: round laces black/green Closing parts: combination of high quality plastic eyelets/textile loops and corrosion resistant metal eyelets
Insock	Replaceable insock made of EVA foam, anatomically shaped, with damping element in ball and heel part
Outsole	PU/PU-sole with flex zone in the ball section PU-midsole, damping impact for joints and spine due to its elastic material PU-outsole: very flexible, slip resistant, SRC, non-marking, integrated H-element for a foot fitting bending and a healthy standing and walking
Toecap	Aluminium Baak flex cap
Anti-penetration	Steel
Plus	Baak® go&relax system Consisting of flex zone , flex cap and H-element for a foot conform bending. Scientifically evaluated positive effects for joints and spine
Sizes/Width	38-48 / 11
Weight	Approx. 590 g / piece (size 42)
Designation	According to EN ISO 20345:2011 S3 SRC ESD
Examples for use	Areas for S2, where the penetration of spiky objects is additionally expected: Building and construction industry, sub construction work, handicraft, steel industry, energy supplier, waste management industry, gas stations, refineries, public transport

BAAK® go&relax system



natural bending line



flex zone in the ball section



foot fitting instead of
straight

Baak GmbH & Co. KG
Hubertusstrasse 3
D-47638 Straelen

Phone: +49/2834/942 41-0
Fax: +49/2834/942 41-69

Email: info@baak.de
Internet: www.baak.de/en

To the movie



Oskar explains the
Baak® go&relax system

Simply better walking. Safetyshoes with mit BAAK® go&relax system.